




UNIT		CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. # WB3171412-DRD-ST		REV. -										
MODEL # eco-ATWB 17-6K14		SCALE NTS			SERIAL #		DATE 11/16/2025										
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]																	
					FACE C  FACE D												
																	
SHIPPING WEIGHT		42740 lbs+ [19390] kg+		OPERATING WEIGHT		59280 lbs+ [26890] kg+		HEAVIEST SECTION WEIGHT		19290 lbs+ [8750] kg+		NO. OF SHIPPING SECTIONS		4		DRAWN BY: SLR	