



UNIT	CLOSED CIRCUIT COOLER		<b>EVAPCO, INC.</b> 	DWG. #	WB3121408-DRC-ST	REV.
MODEL #	eco-ATWB 12-4M14	SCALE NTS		SERIAL #		DATE 2/19/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. \*APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING  
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]



## FACE B



### FACE A

SHIPPING WEIGHT 23160 lbs+ [10510] kg+ OPERATING WEIGHT 34190 lbs+ [15510] kg+ HEAVIEST SECTION WEIGHT 20100 lbs+ [9120] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: SLR