UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-5L18	SCALE NTS

EVAPCO, INC. Evapco


DWG. # WB3121810-DRC-ST REV. SERIAL # DATE_11/11/2025

DRAWN BY:


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]





FACE A





 SHIPPING WEIGHT
 33700 lbs+ [15290] kg+
 OPERATING WEIGHT
 49080 lbs+ [22265] kg+
 HEAVIEST SECTION WEIGHT
 29780 lbs+ [13510] kg+
 NO. OF SHIPPING SECTIONS WEIGHT