UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 17-3I14-Z	SCALE NTS

EVAPCO, INC. Evapco


DWG. # REV. WB3171406-DRD-SF DATE_{11/15/2025} SERIAL #


FACE D


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE
- 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]

FACE C







SHIPPING 27020 lbs+ [12260] kg+ WEIGHT

OPERATING WEIGHT

39620 lbs+ [17975] kg+

HEAVIEST SECTION WEIGHT

11430 lbs+ [5185] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG