UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWR 24-5N14	SCALE NTS


EVAPCO, INC. Evapeo


DWG. # WB3241410-DRC-ST REV. SERIAL # DATE_11/21/2025


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]

FACE C









2'-1 1/4" [643]

> (2) 3" [80] MPT OVERFLOW

> > OPERATING WEIGHT

FACE B

(2) 2" [50] MPT -MAKE-UP

> (2) 3" [80] MPT -DRAIN

> > 77580 lbs+ [35190] kg+

HEAVIEST SECTION WEIGHT

23750 lbs+ [10775] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: