
UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 24-5P20-Z


EVAPCO, INC. Evapea


DWG. # REV. WB3242010-DRC-SF DATE<sub>11/21/2025</sub> SERIAL #

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE
- 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]







**SHIPPING** WEIGHT

75300 lbs+ [34160] kg+

OPERATING WEIGHT

109720 lbs+ [49770] kg+

HEAVIEST SECTION WEIGHT

33140 lbs+ [15035] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG