

UNIT CLOSED CIRCUIT COOLER		<div>EVAPCO, INC.</div> <div>evapco</div>	DWG. # WB3242808-DRC-ST	REV. -
MODEL # eco-ATWB 24-4M28	SCALE NTS		SERIAL #	DATE 9/15/2025

NOTES:
1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]

FACE B

PLAN VIEW

FACE C

FACE D

FACE A

FACE B

2'-6 3/4" [781] *

(8) 4" [100] BFW

FLUID IN

(8) 4" [100] BFW

FLUID OUT

2'-1 1/4" [643]

1'-5" [433]

3 5/8" [92]

(4) 3" [80] MPT OVERFLOW

5 1/8" [130]

24'-1 1/8" [7344]

5'-9 1/4" [1759] *

(8) 4" [100] BFW

FLUID IN

(8) 4" [100] BFW

FLUID OUT

11'-4 3/4" [3473]

11'-5 3/4" [3499]

11'-10" [3607]

3'-3/8" [924] *

9'-1/8" [2748]

6" [154] *

8'-2 1/4" [2494]

4'-8" [1422]

7" [178]

17'-2 3/8" [5242]

FACE A

1'-3 1/4" [387]

(8) 1/2" [15] FPT VENT

1'-4 3/4" [425]

28'-2" [8585]

1'-4 3/4" [425]

SHIPPING WEIGHT 92840 lbs+ [42115] kg+	OPERATING WEIGHT 137100 lbs+ [62190] kg+	HEAVIEST SECTION WEIGHT 20100 lbs+ [9120] kg+	NO. OF SHIPPING SECTIONS 6	DRAWN BY: SLR
-------------------------------------------	---------------------------------------------	--------------------------------------------------	-------------------------------	------------------