NIT CLOSED CIRCUIT COOLER		OOLER	DWG. # WB3TM1806-DRC-SF	REV.
ODEL #	eco-ATWB 10-3N18-Z	SCALE NTS	EVAPCO, INC. EVEPCO SERIAL #	DATE 11/4/2025
2. HÉAVI 3. MPT D BFW D GVD D FLG D PE DE 1. +UNIT ACCE: 5. MAKE 20 psi 6. *-APPI FOR F PIPINO 7. SERIE DRAIN 3. 3/4" [1 RECO 9. DIMEN 1. EXCENTINA DE LA DEL LA	AN MOTOR LOCATION JEST SECTION IS UPPER SECTION INCLUS SECTION IN	AD EAD ELDING DE ' DRAWINGS) 44 kPa] NOT USE JECTING CROSSOVER ES. REFER TO T DRAWING.	FACE B PLAN VIEW FACE B PLAN VIEW FACE A	FACE D
,	4" [100] BFW FLUID IN 1'-10 1/4" * [565] 2" [50] MPT MAKE-UP -1 1/4" [643] 3 5/8"	211 F007 MP7	2'-63/8" * [772] * (4) 4'[100] BFW [2532] FPT VENT (4) 41'[100] BFW [4112] 13'-5 7/8" [4112] AUX. CROSSOVER DRAIN (SEE NOTE 7) 11'-5" [433] T FACE A	
				22.414.51
HIPPING WEIGHT	21350 lbs+ [96		OPERATING 32630 lbs+ [14805] kg+ HEAVIEST SECTION 17700 lbs+ [8030] kg+ NO. OF SHIPPING SECTIONS 2	DRAWN BY: