						IDMC #	logy.
INIT	CLOSED CIRCUIT CO		EVAD(O, INC.	evapco	DWG. # WB3TM2410-DRC-S	
IODEL #	eco-ATWB 10-5K24-Z	SCALE NTS	LVAPC	O, IIIC.		SERIAL #	DATE 11/6/2025
2. HÉAVII 3. MPT D FPT DE BFW D GVD D FLG DI PE DEI 4. +UNIT ACCES 5. MAKE- 20 psi I 6. *-APPF FOR P 7. SERIE: DRAIN 3. 3/4" [15 RECON BE DIMEN E	IN MOTOR LOCATION EST SECTION IS UPPER SEC ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES BEVELED FOR WE ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUD SSORIES (SEE ACCESSORY UP WATER PRESSURE WIN [137 KPa], 50 psi MAX [34 ROXIMATE DIMENSIONS DO RE-FABRICATION OF CONNI S FLOW PIPING AND AUX. C BY OTHERS. DMM] DIA. MOUNTING HOLES MMENDED STEEL SUPPORT SIONS LISTED AS FOLLOWS NGLISH FT-IN	D EAD ILDING DE DRAWINGS) 14 kPa] NOT USE ECTING PIPING ROSSOVER S. REFER TO DRAWING.	PI	FACE B AN VIEW	ACCESS DOOR ACCESS DOOR FAC	ACCESS DOC	FACE D
IV	IETRIC [mm]			1'-3 1/4" [387]			
$1 = \frac{1}{1} = $							Т
	1' [100] BFW	(8) 4" [1] FLUII	9'-8 5/8" [2964] DOUT 15'-10 7/8" [4848] 6" 154] * 6'-2 1/4" [1884] "[80] MPT RFLOW	(8) 1/2" [15] FPT VENT SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7)			
	4 1/4" [108] 5'-11 3/4" [1822]			1'-5" [432]	11'-11 3/4" [3651] 24 [7.	2 1/2" 1'-5" [432	<u></u>

HEAVIEST SECTION WEIGHT

17310 lbs+ [7855] kg+

SHIPPING WEIGHT OPERATING WEIGHT

57620 lbs+ [26140] kg+

39720 lbs+ [18020] kg+

DRAWN BY:

NO. OF SHIPPING SECTIONS