UNIT CLOSED CIRCUIT COOLER			T		®	DWG. # CW4C071808-DRA-SF	REV.
10DEL #	eco-ATWB 7-4H18-Z	SCALE NTS	EVAPO	CO, INC.	evapco	SERIAL #	DATE 12/14/2025
2. HÉAV 3. MPT [FPT D BFW I GVD I FLG D PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. *-APP FOR F PIPIN 7. SERIE DRAIN 8. 3/4" [1 RECC 9. DIMCI	AN MOTOR LOCATION IEST SECTION IS FAN/CAS DENOTES MALE PIPE THRE IENOTES FEMALE PIPE THIS DENOTES BEVELED FOR W DENOTES GROOVED DENOTES PLAIN END WEIGHT DOES NOT INCLUS SSORIES (SEE ACCESSOR -UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 ROXIMATE DIMENSIONS DO PRE-FABRICATION OF CON G S FLOW PIPING AND AUX. N BY OTHERS. 9MM] DIA. MOUNTING HOL MMENDED STEEL SUPPOR NSIONS LISTED AS FOLLOV ENGLISH FT-IN METRIC [mm]	AD READ VELDING JDE Y DRAWINGS) 344 KPa] O NOT USE NECTING CROSSOVER ES. REFER TO RT DRAWING.		FACE B PLAN VIEW	ACCESS D	FACE A	S DOOR FACE D
2" [50 MA 2" [50	100] BFW DIN 2'-3" [686] * 111 1/8" DRAIN 3" [76] - 51/4" [107] 5'-3 5/8 [1616	1" -4" -235]	2'-11 3/8" [899] - 1'-10 7/8" *	SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7) 1'-4 7/8" [429]		_ 18'-0" _ [5486]	
SHIPPING	<u> </u>	<u>CE B</u>	OPERATING 25260 lbc. [11	5051 kg+ HEAVIEST SECTION	N	NO. OF SHIPPING SECTIONS	DRAWN BY:
WEIGHT	19330 lbs+ [8	770] kg+	WEIGHT 25360 lbs+ [11]	505] kg+ WEIGHT	16310 lbs+ [7400] kg+	NO. OF SHIPPING SECTIONS 2	TAM