UNIT CLOSED CIRCUIT COOLER			<u> </u>				DWG. # CW4C072406-DRA-SF REV		
MODEL #	eco-ATWB 7-3J24-Z	SCALE NTS	⊣ E	VAPCO, I	NC. evapco	SER	IAL #		2/14/2025
2. HÉAVII 3. MPT D FPT DE BFW D GVD D FLG DE PE DEI 4. +UNIT ACCES 5. MAKE- 20 psi I 6. *-APPF FOR PI PIPING 7. SERIES DRAIN 8. 3/4" [18	AN MOTOR LOCATION EST SECTION IS FAN/CASIN ENOTES MALE PIPE THREA ENOTES FEMALE PIPE THREA ENOTES FEMALE PIPE THR JENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUI SSORIES (SEE ACCESSORY UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3- ROXIMATE DIMENSIONS DO RE-FABRICATION OF CONN S S FLOW PIPING AND AUX. O BY OTHERS. BY OTHERS. DMM] DIA. MOUNTING HOLE MMENDED STEEL SUPPOR	DE DRAWINGS) 44 kPa] NOT USE ECTING CROSSOVER S. REFER TO		FACE B PLAN VIEW	ACCESS DOOR	CE A	ACCESS DOOR		FACE D
	3/8"	4" * 1'	2'-11 3/8" -10 7/8" ^[899] [581] *	1 ¹ -2" [356]					
(2) 2" [50	1'-7 1/2" * [495] N MPT KE-UP MPT	FLI	[100] BFW UID OUT 4'-7/8" [1241] 12'-1 [36.	SERIES FLOW PIPING L					
1'-11 1/ [587	SRAIN 388 888		5'-1/4" [1530] - 1'-3" - [381] - (2) 3" [80] MPT OVERFLOW	1'-5 1/8" [435]	11'-11 3/4" ————————————————————————————————————	2 1/2" [64]			1'-5 1/8" [435]
SHIPPING	FACE	<u>B</u>	OPERATING		FA	CE A	NO. OF SHIPPING SECTIONS 4	DRAWN BY	,,
WEIGHT	21820 lbs+ [99	ooj ky+	WEIGHT	28800 lbs+ [13065] kg+	WEIGHT 9010 lbs+ [4090] kg	y T	4		· TAM