




UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 7-3H36	SCALE NTS

NOTES:
 1. (M)- FAN MOTOR LOCATION
 2. HEAVIEST SECTION IS FAN/CASING SECTION
 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
 4. +UNIT WEIGHT DOES NOT INCLUDE
 ACCESSORIES (SEE ACCESSORY DRAWINGS)
 5. MAKE-UP WATER PRESSURE
 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
 6. *APPROXIMATE DIMENSIONS DO NOT USE
 FOR PRE-FABRICATION OF CONNECTING
 PIPING
 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
 RECOMMENDED STEEL SUPPORT DRAWING.
 8. DIMENSIONS LISTED AS FOLLOWS:
 ENGLISH FT-IN
 METRIC [mm]

PLAN VIEW



FACE B



FACE A