EVAPCO, INC. Evapeo

DWG. # CW4C073608-DRA-ST REV.
SERIAL # DATE 12/13/2025

DRAWN BY:


TAM


NOTES:

SHIPPING

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]






38660 lbs+ [17540] kg+

OPERATING

WEIGHT

50720 lbs+ [23010] kg+



FACE A

16310 lbs+ [7400] kg+

HEAVIEST SECTION

WEIGHT

NO. OF SHIPPING SECTIONS