
UNIT	CLOSED CIRCUIT COOLER		
MODEL#	eco-ATWB 7-5J14	SCALE NTS	

EVAPCO, INC. Evapeo

## NOTES


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]






**FACE D** 

**FACE A** 





FACE A

SHIPPING WEIGHT 17000 lbs+ [7715] kg+

OPERATING WEIGHT

**FACE B** 

22150 lbs+ [10050] kg+

HEAVIEST SECTION WEIGHT

14810 lbs+ [6720] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG