CLOSED CIRCUIT COOLER	<u> </u>			9	DWG.# CW4C141412-DRB-ST	REV -
100ALE	TS	EVAPCO, 1	INC. eva	000	SERIAL #	DATE: 11/15/2025
NOTES 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAW) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. *-APPROXIMATE DIMENSIONS DO NOT US FOR PRE-FABRICATION OF CONNECTING PIPING 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFE RECOMMENDED STEEL SUPPORT DRAW 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	INGS) SE SE SI SER TO ING.	1'-10 7/8" *	FACE B PLAN VIEV		FACE C (M) ACCESS DOOR CESS DOOR (M) FACE A	FACE D
3'-6" [1067] * (4) 4" [100] BFW FLUID OUT O	73] O O FLUID IN FLUID OUT O O O O O O O O O O O O O O O O O O	[581] 2'-11 3/8" [899] 5'-11 3/8" [1813] 14'-5" [439] 5'-6 1/4" [1683]	FI	1'-2" [355] 1/2" [15] PT VENT	ACCESS DOOR DOOR DOOR DOOR DOOR DOOR DOOR DO	
3" [76] [619] 6'-10 7/8" [2105] 6'-11 3/4" [2127] 7'-4" [2235] 15'-1 [460]	MAKE-UP (2) 2" [50] MPT DRAIN 5 1/8" [130] 1/8"	(2) 3" [80] MPT OVERFLOW		1'-5 1/8" [435]	13'-11 3/4" [4261]	
SHIPPING WEIGHT 38720 lbs+ [17565] kg+	OPERATING WEIGHT	50160 lbs+ [22755] kg+	HEAVIEST SECTION 171	70 lbs+ [7790] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG