


UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 14-6K14-Z	SCALE NTS


1

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -\*APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING  
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN  
METRIC [mm]




## FACE C



**FACE D**



## FACE A



## FACE A

SHIPPING WEIGHT 38660 lbs+ [17540] kg+ OPERATING WEIGHT 50100 lbs+ [22725] kg+ HEAVIEST SECTION WEIGHT 17140 lbs+ [7775] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: JLG