EVAPCO, INC. MODEL # N.T.S. UNIT SERIAL # EGH1220MR-DRB-ST CLOSED CIRCUIT COOLER eco-ATWB-H 12-2L20-U22 11/3/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH IN** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY FACE 2 DRAWINGS) **PLAN VIEW** 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 1 69 3/8 1762] 45 [1142] - . 7 [179] (2) 1/2 [15] FPT VENT 56 1/4 [1427] (2) 4 [100] BFW 5 1/2 INLET [140] **CROSSOVER PIPING** 36 3/8 [922] 33 1/2 36 3/8 ₋ 851] [922] 13 3/4 83 9/32 213 7/8 [349] [2115] **ACCESS** [5432] **DOORS** (2) 4 [100] BFW OUTLET 5 7/8 [149] 2 [50] MPT 74 1/8 [1883] MAKE-UP 25 1/4 [641] 3 [80] MPT 17 [432] 4 1/4 [108] 3 5/8 [92] DRAIN 19 1/4 [489] 20'-0" [6096] 5 1/4 [133] 3 [80] MPT 86 [2184] **OVERFLOW** FACE 1 11'-10" 3607 FACE 2 SHIPPING OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: HEAVIEST SECTION SFR 27850 lbs+ [12635] kg+ 40820 lbs+ [18520] kg+ 19470 lbs+ [8830] kg+ WEIGHT WEIGHT WEIGHT