UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 9-4I9-Z

EVAPCO, INC. evapco



DWG. # REV. WB3090908-DRC-SF DATE_{11/22/2025} SERIAL #


NOTES:

- 1. (M) FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN METRIC [mm]





FACE C



FACE D

FACE A





SHIPPING WEIGHT

11080 lbs+ [5030] kg+

OPERATING WEIGHT

15480 lbs+ [7025] kg+

HEAVIEST SECTION WEIGHT

9640 lbs+ [4375] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG