UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-3J12-Z	SCALE NTS

EVAPCO, INC. Evapco

DWG. # REV. WB3121206-DRC-SF DATE 11/8/2025 SERIAL #


NOTES:


- 1. (M) FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN METRIC [mm]



FACE C





(1) (2) 1/2" [15] **FPT VENT** SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7) **FACE A**

SHIPPING WEIGHT

16950 lbs+ [7690] kg+

OPERATING WEIGHT

25570 lbs+ [11600] kg+

HEAVIEST SECTION WEIGHT

14240 lbs+ [6460] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: TLM