UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-4M12-Z	SCALE NTS

EVAPCO, INC. Evapco

DWG. # REV. WB3121208-DRC-SF DATE 11/10/2025 SERIAL #

## NOTES:


- 1. (M) FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS:

**ENGLISH FT-IN** METRIC [mm]





**FACE B** 

**PLAN VIEW** 



**FACE A** 





**SHIPPING** WEIGHT

20280 lbs+ [9200] kg+

**OPERATING** WEIGHT

29720 lbs+ [13485] kg+

HEAVIEST SECTION WEIGHT

17570 lbs+ [7970] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG