
UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. Evapco			DWG. # WB3121412-DRC-SF		REV	
MODEL #	eco-ATWB 12-6N14-Z SCALE NTS					SERIAL #		DATE _{11/13/2025}	
2. HÉAVI 3. MPT D FPT D BFW L GVD D FLG D PE DE 4. + UNIT ACCE FOR A 5. MAKE 20 psi 6. * - APF FOR P PIPINO 7. SERIE DRAIN 8. 3/4" [1' RECO	FAN MOTOR LOCATION IEST SECTION IS UPPER SE DENOTES MALE PIPE THREA DENOTES FEMALE PIPE THREA DENOTES BEVELED FOR WE DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END T WEIGHT DOES NOT INCLU ESSORIES (SEE SEPARATE I ACCESSORIES) E-UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [34 PROXIMATE DIMENSIONS DO PRE-FABRICATION OF CONN G ES FLOW PIPING AND AUX. CO N BY OTHERS 9MM] DIA. MOUNTING HOLE DIMMENDED STEEL SUPPORT NSIONS LISTED AS FOLLOW ENGLISH FT-IN [METRIC] MM	D EAD ELDING DE DRAWINGS 14 kPa] D NOT USE ECTING EROSSOVER S. REFER TO DRAWING.	7"[178]	FACE B PLAN VIEW		FACE A	FACE D		
	(4) 4" [100] BFW FLUID IN 3'-11 3/4" * [1213]	5'-9 1/4" * 1759] * 1	3'-3/8" * [924] * 10'-5 1/8" [3180] * (4) 4" [100] BFW FLUID OUT	(4) 1/2 FPT \ 3/8" SERIES FLOW PIP 12.] (SEE NOT	ING E 7)				



SHIPPING WEIGHT 30860 lbs+ [14000] kg+ OPERATING WEIGHT 43780 lbs+ [19860] kg+ HEAVIEST SECTION WEIGHT 27800 lbs+ [12610] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLG