UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 10-3I36-7	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # WB3TM3606-DRC-SF REV. SERIAL # DATE_{12/14/2025}

DRAWN BY:

NO. OF SHIPPING SECTIONS

NOTES:

SHIPPING

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.


OPERATING


WEIGHT

64400 lbs+ [29215] kg+

41840 lbs+ [18980] kg+

9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]





HEAVIEST SECTION

WEIGHT

17270 lbs+ [7835] kg+