


UNIT	CLOSED CIRCUIT COOLER		 [®]	DWG. #	WB36M1212-DRC-SF	REV.	-
MODEL #	eco-ATWB 20-6L12-Z	SCALE NTS		SERIAL #		DATE	2/11/2026


EVAPCO, INC.

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. SERIES FLOW PIPING AND AUX. CROSSOVER
DRAIN BY OTHERS.
8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
9. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



FACE B



FACE A

SHIPPING WEIGHT 45040 lbs+ [20430] kg+ OPERATING WEIGHT 64000 lbs+ [29030] kg+ HEAVIEST SECTION WEIGHT 19960 lbs+ [9055] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: SLR