




UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 20-4I24-Z	SCALE NTS

**EVAPCO, INC.** 

DWG. #	WB36M2408-DRC-SF	REV. -
SERIAL #		DATE 2/13/2026

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]



SHIPPING  
WEIGHT

69380 lbs+ [31475] kg+

OPERATING  
WEIGHT

102000 lbs+ [46270] kg+

HEAVIEST SECTION  
WEIGHT

14640 lbs+ [6645] kg+

NO. OF SHIPPING SECTIONS

6

DRAWN BY:  
SLR