



UNIT	CLOSED CIRCUIT COOLER		 <sup>®</sup>	DWG. #	WB36M3606-DRC-SF	REV.	-
MODEL #	eco-ATWB 20-3J36-Z	SCALE NTS		SERIAL #		DATE	2/14/2026

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. \*-APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING  
PIPING
7. SERIES FLOW PIPING AND AUX. CROSSOVER  
DRAIN BY OTHERS.
8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
9. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]



## FACE B



## FACE A



## FACE A

SHIPPING WEIGHT 84880 lbs+ [38505] kg+ OPERATING WEIGHT 130320 lbs+ [59115] kg+ HEAVIEST SECTION WEIGHT 17400 lbs+ [7895] kg+ NO. OF SHIPPING SECTIONS 6 DRAWN BY: SLR