


UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-ATWB 7-6H18

EVAPCO, INC. 


DWG. #	CW4C071812-DRA-ST	REV.	-
SERIAL #		DATE	2/4/2026

NOTES:
1. (M) FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN
METRIC [mm]



FACE B



PLAN VIEW



FACE A

SHIPPING WEIGHT	25190 lbs+ [11430] kg+	OPERATING WEIGHT	32710 lbs+ [14840] kg+	HEAVIEST SECTION WEIGHT	22170 lbs+ [10060] kg+	NO. OF SHIPPING SECTIONS	2	DRAWN BY: TAM
-----------------	------------------------	------------------	------------------------	-------------------------	------------------------	--------------------------	---	---------------