UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 14-4J12

EVAPCO, INC. Evapeo




REV. CW4C141208-DRA-ST

SERIAL #


DATE_{11/14/2025}


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



DWG. #





SHIPPING WEIGHT

25740 lbs+ [11680] kg+

OPERATING WEIGHT

33700 lbs+ [15290] kg+

HEAVIEST SECTION WEIGHT

10970 lbs+ [4980] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM