

UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-ATWB 7-5K14

EVAPCO, INC. 

DWG. # CW4C071410-DRA-ST

REV -


SERIAL #

DATE: 2/5/2026

NOTES

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN
METRIC [mm]




FACE B

FACE B
PLAN VIEW

FACE C



FACE D



FACE A

SHIPPING
WEIGHT

17060 lbs+ [7740] kg+

OPERATING
WEIGHT

22210 lbs+ [10075] kg+

HEAVIEST SECTION
WEIGHT

14870 lbs+ [6745] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG