

UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-ATWB 7-3J14-Z

EVAPCO, INC. 

DWG. # CW4C071406-DRA-ST


REV -

SERIAL #

DATE: 2/5/2026


NOTES

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]




FACE B


FACE B
PLAN VIEW



FACE C



FACE D



FACE A

SHIPPING
WEIGHT

12490 lbs+ [5670] kg+

OPERATING
WEIGHT

16490 lbs+ [7480] kg+

HEAVIEST SECTION
WEIGHT

10300 lbs+ [4675] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG