



UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-ATWB 7-3J28-Z

EVAPCO, INC. 


DWG. #	CW4C072806-DRA-ST	REV	-
SERIAL #		DATE:	2/5/2026

NOTES

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS FAN/CASING SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



FACE B



FACE A

SHIPPING
WEIGHT

24980 lbs+ [11335] kg+

OPERATING
WEIGHT

32980 lbs+ [14960] kg+

HEAVIEST SECTION
WEIGHT

10300 lbs+ [4675] kg+

NO. OF SHIPPING SECTIONS

4

DRAWN BY: **JLG**