EVAPCO, INC.

UNIT MODEL # SERIAL # N.T.S. TLEOP1836-DRA-ST **COOLING TOWER** LSTE-8P518 12/13/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 7'-10" FACE 1 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE **PLAN VIEW** 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 18'-0" 5486] FACE 2 94 [2388] 108 [2743] 11 3/8 [290] ∠8 [200] BFW/GVD **INLET** 74 7/8 [1901] (2) ACCESS DOOR -13'-6 1/4" [4120] 3 [80] MPT 2 [50] MPT **OVERFLOW** 87 3/8 [2219] MAKE-UP 35 1/2 [902] 21 3/8 **[** 543] <u>DRAIN</u> 7 5/8 18'-0" [194] [5486] 3 1/8 [79] 23 5/8 FACE 2 [178] [600] 40 3/8 8 [200] BFW/GVD [1026] 44 3/8 [1127] OUTLET 7'-10" [2388] FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 8440 lbs+ [3828] kg+ 13790 lbs+ [6255] kg+ 5440 lbs+ [2468] kg+ 2 WEIGHT WEIGHT WEIGHT