## EVAPCO, INC. UNIT MODEL # SERIAL # TLE041224-DRA-ST N.T.S. **COOLING TOWER** LSTE-4112 12/8/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING 4'-5/8" [ 1234 ] GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 1 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO **PLAN VIEW** RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 7 5/8" FROM CONNECTION END OF UNIT 11'-11 1/2" 3645 FACE 2 10 1/2 [ 267 ] 6 [150] BFW/GVD **INLET** 3 76] 62 7/8 [ 1597 ] (2) ACCESS DOORS 8'-10 3/8" [ 2702 ] 3 [80] MPT **OVERFLOW** 20 1/8 <sub>[</sub> 511 ] 1 [25] MPT -2 [50] MPT MAKE-UP DRAIN 43 1/2 [ 1105 ] 26 1/8 [ 664 ] (M)(M)11 7/8 -6 [ 152 ] 15 3/4 \_ 6 [150] BFW/GVD [ 400 ] OUTLET 3 [ 76 ] 20 7/8 [530] 11'-11 1/2" <sub>[</sub> 3645 ] 1 3/4 [ 44 ] 19 1/8 [ 1234 ] [ 486 ] FACE 2 FACE 1 SHIPPING OPERATING HEAVIEST SECTION NO. OF SHIPPING SECTIONS 2930 lbs+ [1329] kg+ 4240 lbs+ [1923] kg+ 1730 lbs+ [785] kg+ 2 WEIGHT WEIGHT WEIGHT