EVAPCO, INC.

UNIT MODEL # SERIAL # N.T.S. TLE041824-DRA-ST **COOLING TOWER** LSTE-4118 12/8/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD 4'-5/8" [1234] BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 1 (M) 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 7 5/8" 18'-0" FROM CONNECTION END OF UNIT [5486] FACE 2 22 7/8 581] 10 1/2 6 [150] BFW/GVD [267] INLET (2) ACCESS 3 [80] MPT 62 7/8 [1597] **DOORS OVERFLOW** 8'-10 3/8" [2702] 20 1/8 _ [511] 1 [25] MPT -2 [50] MPT MAKE-UP DRAIN 43 1/2 [1105] H 26 1/8 (M) \mathbb{M} [664] 11 7/8 6 [152] [302] 15 3/4 [400] 6 [150] BFW/GVD 3 [76] OUTLET 20 7/8 [530] 1 3/4 [44] 18'-0" 19 1/8 [5486] 1234 [486] FACE 2 FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 4330 lbs+ [1964] kg+ 6330 lbs+ [2871] kg+ 2580 lbs+ [1170] kg+ 2 WEIGHT WEIGHT WEIGHT