




# EVAPCO, INC.



UNIT	COOLING TOWER	MODEL #	LSTE-4118U	SCALE	N.T.S.	DWG. #	TLE041824-DRA-ST	REV.	-	DATE	2/4/2026	SERIAL #
------	---------------	---------	------------	-------	--------	--------	------------------	------	---	------	----------	----------

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS LOWER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED FOR VICTAULIC
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING
7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN  
[METRIC] [mm]
8. MAKE-UP CONNECTION LOCATED 7 5/8"  
FROM CONNECTION END OF UNIT



SHIPPING WEIGHT 4330 lbs+ [1964] kg+ OPERATING WEIGHT 6330 lbs+ [2871] kg+ HEAVIEST SECTION WEIGHT 2580 lbs+ [1170] kg+ NO. OF SHIPPING SECTIONS 2