EVAPCO, INC.



UNIT MODEL # SERIAL # N.T.S. TLEOP1248-DRA-ST **COOLING TOWER** LSTE-8P412L 12/14/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 7'-10" <u>FACE</u> 1 ^[2388] 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE **PLAN VIEW** 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 11'-11 3/4" [3651] FACE 2 7/8 [21] 94 [2388] 71 7/8 [1826] 11 3/8 [290] ∠8 [200] BFW/GVD INLET 86 7/8 [2206] (2) ACCESS DOOR -14'-6 1/4" [4425] 3 [80] MPT 2 [50] MPT **OVERFLOW** MAKE-UP 87 3/8 [2219] 35 1/2 [902] — 2 [50] МРТ_□ T_| 21 3/8 _**▼**[543] DRAIN 7 5/8 2 1/2 [63] 11'-11 3/4" 3651] [194] 3 1/8 [79] 23 5/8 FACE₂ [178] 600] 40 3/8 8 [200] BFW/GVD [1026] 44 3/8 [1127] OUTLET 7'-10" [2388] FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 6390 lbs+ [2898] kg+ 9870 lbs+ [4477] kg+ 3600 lbs+ [1633] kg+ 2 WEIGHT WEIGHT WEIGHT