EVAPCO, INC. EVAPCO, INC. SOME PARTY SOME PARTY SOME PARTY SOME NTS SOME AT THE BOOK SOME PARTY	JNIT	COOLING TOWER		EVADOO TI	vo evapco	DWG. # TV03062P-DRD-ST	REV
1. (b) Fack mytoria (DOCATION) FACE C FACE C	MODEL #	LPT-346	SCALE NTS	EVAPCO, II	NC.	SERIAL #	DATE 12/4/2025
3'-10-1/4" (1176) 4" [100] MPT INLET (1270) 4. CCESS DOOR 2" [50] MPT OVERFLOW OVERFLOW (1270) 4. CCESS DOOR DOOR DOOR IN [25] MPT MAKE-UP (1270) 4. CCESS DOOR IN [25] MPT MAKE-UP (1270) 4. COESS DOOR IN [25] MPT MAKE-UP (1270) 4. COESS DOOR IN [25] MPT MAKE-UP (1270) 4. COESS DOOR IN [25] MPT MAKE-UP (103)	1. (M)- FA 2. MPT DE FPT DE BFW D GVD DI FLG DE 3. + UNIT ACCES: FOR AC 4. 3/4" DI RECOM DRAWI 5. MAKE-U 50 psi 6. DIMEN.	ENOTES MALE PIPE THREAD INOTES FEMALE PIPE THREAD ENOTES BEVELED FOR WELDING ENOTES GROOVED ENOTES FLANGE WEIGHT DOES NOT INCLUDE SORIES (SEE SEPARATE DRAWING CCESSORIES) A. MOUNTING HOLES. REFER TO IMENDED STEEL SUPPORT NG JIP WATER PRESSURE-20 psi MIN, MAX SIONS LISTED AS FOLLOWS: NGLISH FT-IN					FACE D
SHIPPING 1620 Ibox 1725 Ikg. OPERATING 2500 Ibox 1475 Ikg. HEAVIEST SECTION 1620 Ibox 1725 Ikg. NO. OF SHIPPING SECTIONS 1 DRAWN BY:		3'-10 1/4" [1176] 3'-104" [1176] 3 1/4" [100] M OUTLET 4 3/4" [121] 5 1/2" [140] 3'-4 3 [103	PT	6'-10 1/2" [2096] 8 3/4" [222] 1'-8 1/8" [511] 1 3/8" [35]	DOOR 2" [50] MPT OVERFLOW 2" [50] MPT DRAIN 2'-1/4" DRAIN 2'-1/4" [616] 2'-8 1/4" [819] 5'-6" [1676]	ACCESS DOOR 1" [25] MPT MAKE-UP 7/8" 66] E A	5'-3 7/8" [1622]