UNIT COOLING TOWER	FVADCO INC evap	DWG. # AX122209-DRC-ST REV.
MODEL # SCALE AXS 12-11I22	EVAPCO, INC.	SERIAL # DATE 12/14/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 4. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 5. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm]	FACE B PLAN VIEW 5'-11" [1804] 0	FACE C ACCESS DOOR (2) 8" [200] ASME 150 BOLT PATTERN INLET FACE D
7" [178] 11'-10" [3607] FACE B	11'-4 1/4" [3461] ACCESS D 10" [250] BFW/O OUT 3/8" [692] 1'-6 7/8" [479] 8 1/2" [216] 3 3/8" [86]	
SHIPPING WEIGHT 11860 lbs+ [5380] kg+ OPERAT WEIGH	ING 26060 lbs+ [11825] kg+ HEAVIEST SECTION 11860	O lbs+ [5380] kg+ No. of shipping sections 1 DRAWN BY: JLM