UNIT CONDENSER			EVADOO T	NC evapco	DWG. # WV050606-DRC-ST	REV.
MODEL #	LRC-76	^{ALE} NTS	EVAPCO, I	NC. Evapeo	SERIAL #	DATE _{11/26/2025}
FPT DENOTES BFW DENOTES GVD DENOTES FLG DENOTES PE DENOTES 3. +UNIT WEIGHT ACCESSORIES 4. 3/4" [19mm] DIA RECOMMENDE 5. DIMENSIONS L 6. * - APPROXIMA USE FOR PRE- 7. MAKE-UP WAT	MALE PIPE THREAD FEMALE PIPE THREAD S BEVELED FOR WELDING G GROOVED FLANGE PLAIN END DOES NOT INCLUDE GSEE ACCESSORY DRAV A MOUNTING HOLES. REF ED STEEL SUPPORT DRAV ISTED AS FOLLOWS: ENG ME TE DIMENSIONS DO NOT FABRICATION OF CONNE	VINGS) FER TO WING GLISH FT IN TRIC] [mm]	FACE B 5-5/8" [1540]	FACE C		FACE D
-	2'-6 3/8" * [770]			12'-2 7/8 [3731] FACE A	6'-3"	
4" [100] PE — REFRIG IN 4" [100] PE — REFRIG OUT			3'-7 1/2" [1106] 1'-7 1/2" * [495] * 6'-7 3/4" [2026]	ACCESS DOOR		6'-7 3/4" [2026]
3" [80] MPT — OVERFLOW		(\(\) \(\	3'-1/4" [919] 8 3/4" [222]	[5'-6"	" [25] MPT 1AKE-UP	-ACCESS DOOR
2" [50] MPT — DRAIN	5'-5/8" [1540] FACE B	-	1'-1 5/8"	12'-2 7/8 [3731] FACE A		
SHIPPING WEIGHT	4040 lbs+ [1835] kg+		OPERATING 5910 lbs+ [2685] kg+	HEAVIEST SECTION 4040 lbs+ [1835] kg+	NO. OF SHIPPING SECTIONS 1	PRAWN BY: TLS