


EVAPCO, INC.





UNIT EVAPORATIVE CONDENSER	MODEL # eco-PMC-831	SCALE N.T.S.	DWG. # ECETM1812-DRA-ST	REV. -	DATE 12/13/2025	SERIAL #
--------------------------------------	------------------------	-----------------	----------------------------	-----------	--------------------	----------

- NOTES:
1. (M)- FAN MOTOR LOCATION
 2. HEAVIEST SECTION IS UPPER SECTION
 3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
 4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
 5. 3/4" DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
 6. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
 7. *-APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN
[METRIC] [mm]



**FACE 1
PLAN VIEW**



SHIPPING WEIGHT	35890 lbs+ [16279] kg+	OPERATING WEIGHT	42560 lbs+ [19305] kg+	HEAVIEST SECTION WEIGHT	28090 lbs+ [12741] kg+	NO. OF SHIPPING SECTIONS	2
-----------------	------------------------	------------------	------------------------	-------------------------	------------------------	--------------------------	---