EVAPCO, INC.

MODEL # UNIT SERIAL # N.T.S. EGH241802-DRD-ST CLOSED CIRCUIT COOLER eco-ATWB-H 24-1L18-U34 12/13/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH IN** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 2 **PLAN VIEW** 24'-1 1/8" [7344] 69 3/8 [1762] FACE 1 27 5/8 * 702] 7 [178] (4) 1/2 [15] FPT VENT -(4) 4 [100] BFW INLET 56 1/4 [1427] (11) CROSSOVER -6 7/8 113 3/4 * **PIPING** 2888] [175] **ACCESS** 44 3/8 * 1126] 33 1/2 851] **DOORS** 75 1/32 5 1/2 (4) 4 [100] BFW [1906] 229 5/8 [140] OUTLET [5832] 5 7/8 [149] 98 1/8 [2492] 25 1/4 [641] 5 1/4 [133] 3 5/8 [[92] [432] 4 1/4 (2) 3 [80] MPT (2) 2 [50] MPT 19 [483] [108] **OVERFLOW** 56 [1422] [5486] MAKE-UP (2) 3 [80] MPT FACE 1 [3607] DRAIN FACE 2 SHIPPING OPERATING HEAVIEST SECTION NO. OF SHIPPING SECTIONS DRAWN BY: SFR 43360 lbs+ [19670] kg+ 64520 lbs+ [29270] kg+ 14060 lbs+ [6380] kg+ WEIGHT WEIGHT WEIGHT