
UNIT	CONDENSER	
MODEL #	eco-ATC-636A	SCALE NTS

EVAPCO, INC. Evapco


DWG. # WB3091812-DRC-ST REV. SERIAL # DATE<sub>12/15/2025</sub>


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]



FACE A





SHIPPING WEIGHT

28170 lbs+ [12780] kg+

OPERATING WEIGHT

34850 lbs+ [15810] kg+

HEAVIEST SECTION WEIGHT

25380 lbs+ [11515] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: SLR