## EVAPCO, INC.



UNIT MODEL # SERIAL # REV. N.T.S. EGH2414MR-DRE-ST 10/26/2025 CLOSED CIRCUIT COOLER eco-ATWB-H 24-4L14-U22 NOTES: 1. (M)- FAN MOTOR LOCATION 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER 2. HÉAVIEST SECTION IS COIL SECTION TO RECOMMENDED STEEL SUPPORT DRAWING. 3. MPT DENOTES MALE PIPE THREAD 7. \* - APPROXIMATE DIMENSIONS DO FPT DENOTES FEMALE PIPE THREAD NOT USE FOR PRE-FABRICATION BFW DENOTES BEVELED FOR WELDING OF CONNECTING PIPING. **GVD DENOTES GROOVED** FLG DENOTES FLANGE +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 2 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** FACE 1 5 1/8 [ 130 ] 27 5/8 702 ] 7 [ 178 ] (4) 1/2 [15] FPT VENT (4) 4 [100] BFW 56 1/4 (11) (M) CROSSOVER ÌNLET 51/2 -**PIPING ACCESS** 105 3/4 \* 2684 ] 33 1/2 851 **DOORS** 30 3/4 100 9/32 36 3/8 \* [ 922 ] 242 7/8 (4) 4 [100] BFW 5 7/8 \* [ 149 ] ÒÚTLĒT 86 1/8 [ 2188 ] 25 1/4 [ 641 ] 5 1/4 [ 133 ] 3 5/8 [ 92 ] [ 432 ] 4 1/4 [ 108 ] (2) 3 [80] MPT (2) 2 [50] MPT **OVERFLOW** 4261] MAKE-UP 142 [ 3607 ] (2) 3 [80] MPT FACE 1 DRAIN FACE 2 OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: **SHIPPING** HEAVIEST SECTION SFR 21500 lbs+ [9755] kg+ 55420 lbs+ [25140] kg+ 77440 lbs+ [35130] kg+ WEIGHT WEIGHT WEIGHT