UNIT	CONDENSER	
MODEL #	eco-ATC-300A	SCALE NTS

EVAPCO, INC. Evapeo


WG. #	EGTM1204-DRC-ST	REV.
ERIAL #		DATE 11/1/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN METRIC [mm]


FACE C



FACE D

FACE A





SHIPPING WEIGHT

12200 lbs+ [5535] kg+

OPERATING WEIGHT

ATING 17920 lbs+ [8130] kg+

HEAVIEST SECTION WEIGHT

9650 lbs+ [4380] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: