UNIT	JNIT COOLING TOWER	
MODEL #	SUN-19-611	SCALE NTS


EVAPCO, INC. Evapeo


DWG. # T3091148-DRB-SUN REV. SERIAL # DATE 11/26/2025


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN

[METRIC] MM







SHIPPING WEIGHT 6000 lbs+ [2725] kg+ OPERATING WEIGHT

9030 lbs+ [4100] kg+

HEAVIEST SECTION WEIGHT

2580 lbs+ [1170] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: