EVAPCO, INC. UNIT MODEL # SERIAL # N.T.S. TLE041836-DRA-ST **COOLING TOWER** LSTE-4218 12/13/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD 4'-5/8" [1234] BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 1 (M) 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 8. MAKE-UP CONNECTION LOCATED 7 5/8" 18'-0" FROM CONNECTION END OF UNIT 5486] FACE 2 10 1/2 6 [150] BFW/GVD [267] INLET ³ ⁷ ⁷ 74 7/8 [1902] (2) ACCESS 3 [80] MPT DOORS 9'-10 3/8" **OVERFLOW** [3007] 20 1/8 ₋ [511] 1 [25] MPT -2 [50] MPT MAKE-UP DRAIN 43 1/2 [1105] 26 1/8 [664] **M** (M) 11 7/8 6 [152] [302] 15 3/4 [400] 3 [76] 6 [150] BFW/GVD OUTLET 20 7/8 [530] 1 3/4 [44] 18'-0' 19 1/8 [5486] [486] FACE 2 FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 4630 lbs+ [2100] kg+ 6630 lbs+ [3007] kg+ 2610 lbs+ [1184] kg+ 2 WEIGHT WEIGHT WEIGHT