UNIT	CONDENSER		EVADO	O TNC	vapco	DWG. # WV051212-DRC-ST	REV
MODEL #	LRC-246	SCALE NTS	EVAPC	O, INC.		SERIAL #	DATE <sub>11/26/2025</sub>
2. MPT DE FPT DE BFW DE GVD DE FLG DE PE DEN 3. +UNIT V ACCES 4. 3/4" [19, RECOM 5. DIMENS 6. * - APPF USE FC 7. MAKE-L	N MOTOR LOCATION ENOTES MALE PIPE THREATH PROTES FEMALE PIPE THREATH PROTES BEVELED FOR WISHOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU SORIES (SEE ACCESSOR) mm] DIA. MOUNTING HOLE IMENDED STEEL SUPPOR SIONS LISTED AS FOLLOW ROXIMATE DIMENSIONS D DR PRE-FABRICATION OF O JP WATER PRESSURE 137 kPa] MIN, 50 psi [344 kF	READ ELDING  DE Y DRAWINGS) ES. REFER TO T DRAWING YS: ENGLISH FT IN [METRIC] [mm] O NOT CONNECTING PIPING	FACE B [1540]  B PLAN VIEW		FACE C  18'-2.5/8" [5553]  FACE A		FACE D
4" [ REFR 3 1 [ 8.	[80] MPT	3'-6" [ 1067 ]	8'-7 1/4" [ 2623 ]  5 1/4" *		ACCESS DOOR  11'-5 3/4" [ 3499 ]  18'-2 5/8" [ 5553 ]  FACE A	1" [25] MPT MAKE-UP	6'-7 3/4" [ 2026 ] 1'-8 1/8" [ 511 ] ACCESS DOOR
SHIPPING WEIGHT	9770 lbs+ [44	35] kg+	PERATING 13880 lbs+ [6300]	kg+ HEAVIEST SECTION WEIGHT	9770 lbs+ [4435] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: TLS