UNIT	CONDENSER	
MODEL #	eco-ATC-632A	SCALE NTS


EVAPCO, INC. Evapeo

DWG. # WB3121212-DRC-ST REV. SERIAL # DATE\_12/14/2025


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
  PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]

## **FACE C**



**FACE A** 





OPERATING WEIGHT

33840 lbs+ [15350] kg+

HEAVIEST SECTION WEIGHT

23970 lbs+ [10875] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: