UNIT CONDENSER		EVAD	CO TN	evanço °	DWG. #	WB3122806-DRC-ST	REV	
MODEL #	eco-ATC-942A	SCALE NTS	EVAP	CO, IN	C. evapeo	SERIAL #		DATE <sub>11/26/2025</sub>
2. HEAVIE 3. MPT DI FPT DE BFW D GVD DI FLG DE PE DEN 4. +UNIT N ACCES 5. MAKE-I 20 psi N 6. *-APPR FOR PF PIPING 7. 3/4" [19 RECON	IN MOTOR LOCATION EST SECTION IS UPPER SECENOTES MALE PIPE THREAD	D EAD ELDING  DE DRAWINGS)  14 kPa] NOT USE ECTING  S. REFER TO DRAWING.		FACE B PLAN VIEW	ACCESS DOOR	ACE C	ACCESS DOOR	FACE D
			7" [ [ 178]	11.2.1/41				
	T — —		+ +	1'-3 1/4" _ [ 387 ]		<del> </del>		
1'-10 [ 56 7 (2) 2" [50] MAK 1 2'-1 1/4" [ 643]	5'-9 1/4 [ 1759 LO 1/4" * (4) 4* [100] PE 565] (4) 4* [100] PE	REFRIG IN REFRIG OUT	3'-3/8" *				(M)	
	50] MPT — AKE-UP		6" *					
<b>↑</b> 3 [:	5/8"   C (2) 3" [80] MPT DRAIN   5 1/4"   133   4 1/4"   108		1'-5" [ 433 ] (2) 3" [80] MPT OVERFLOW		12  11 2/4	2.1/2"		
	7'-2"	-		1'-4 3 <i>/4</i> "	13'-11 3/4" [ 4261 ]	2 1/2" [ 64 ]		1'-4 3/4"
	11'-10 [ 3607 <b>FACE</b>			1'-4 3/4" [425]			-	1'-4 3/4" [ 425]
SHIPPING WEIGHT	38520 lbs+ [174]	75] kg+	OPERATING 54100 lbs+ [2	24540] kg+	EAVIEST SECTION 16200 lbs+ [7350] kg-	NO. C	OF SHIPPING SECTIONS 4	ORAWN BY: SLR