

UNIT		CONDENSER		<div>EVAPCO, INC.</div> <div><div>evapco</div></div>	DWG. #	WB3171212-DRD-ST		REV.	-								
MODEL #		eco-ATC-857A			SCALE	NTS		SERIAL #	DATE 7/7/2025								
<div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div> FPT DENOTES FEMALE PIPE THREAD</div> <div> BFW DENOTES BEVELED FOR WELDING</div> <div> GVD DENOTES GROOVED</div> <div> FLG DENOTES FLANGE</div> <div> PE DENOTES PLAIN END</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div> 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING</div> <div>7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>8. DIMENSIONS LISTED AS FOLLOWS:</div> <div> ENGLISH FT-IN</div> <div> METRIC [mm]</div>																	
<div>PLAN VIEW</div> <div><div>FACE B</div><div>FACE C</div><div>FACE D</div><div>FACE A</div></div>					<div><div>FACE B</div><div>FACE A</div></div>												
<div><div>FACE B</div><div><div><div>1'-9 3/8" [543]</div><div>3'-6" [1067] *</div><div>1'-11 1/8" [589]</div><div>3" [76]</div><div>17'-4 1/8" [5286]</div><div>5 1/8" [130]</div><div>8'-1 1/4" [2445]</div><div>8'-1 1/4" [2470]</div><div>8'-5 1/2" [2578]</div><div>2" [50] MPT MAKE-UP</div><div>2" [50] MPT DRAIN</div><div>(2) 3" [80] MPT OVERFLOW</div><div>(4) 4" [100] PE REFRIG IN</div><div>(4) 4" [100] PE EFRIG OU</div><div>(4) 4" [100] PE REFRIG IN</div><div>(4) 4" [100] PE EFRIG OU</div><div>6" [154] *</div><div>2'-10 1/4" [870]</div><div>1'-3" [383]</div><div>8'-10" [2694]</div><div>13'-10 1/4" [4223]</div><div>4'-3/4" [1238] *</div><div>2'-2 3/8" [670] *</div></div></div></div>					<div><div>FACE A</div><div><div>1'-7/8" [327]</div><div>1'-3 5/8" [397]</div><div>11'-11 3/4" [3651]</div></div></div>												
SHIPPING WEIGHT		37420 lbs+ [16975] kg+		OPERATING WEIGHT		46260 lbs+ [20985] kg+		HEAVIEST SECTION WEIGHT		16840 lbs+ [7640] kg+		NO. OF SHIPPING SECTIONS		4		DRAWN BY: SLR	