JNIT CONDENSER		FV/A DCC	EVAPCO, INC. evapco			DWG. # WB3241412-DRC-ST		REV.	
IODEL #	eco-ATC-1219A	SCALE NTS	EVAPCO), INC.		SER.	IAL #		DATE 11/26/2025
2. HÉAVI 3. MPT D FPT DI BFW C GVD D FLG DI PE DE 4. +UNIT ACCES 5. MAKE- 20 psi 6. *-APPF FOR P PIPINO 7. 3/4" [11 RECOI	AN MOTOR LOCATION EST SECTION IS UPPER S ENOTES MALE PIPE THRE ENOTES FEMALE PIPE TH ENOTES BEVELED FOR V ENOTES FLANGE NOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCL SSORIES (SEE ACCESSOF UP WATER PRESSURE MIN [137 kPa], 50 psi MAX ROXIMATE DIMENSIONS D RE-FABRICATION OF CON G 9mm] DIA. MOUNTING HOL MMENDED STEEL SUPPOI ISIONS LISTED AS FOLLO' ENGLISH FT-IN METRIC [mm]	EAD READ READ VELDING UDE RY DRAWINGS) 344 kPa] O NOT USE INECTING LES. REFER TO RT DRAWING.			FACE B PLAN VIEW		C2) ACCESS DOOR	FACE D	
				7" [178	3] 1'-3 1/4"		FACE A	J	
	3'-11 3/4" *	(2) 2" [50] MPT MAKE-UP (2) 3" [80] MPT DRAIN 5 1/8" [130]	(4) 4" [100] PE REFRIG OUT (4) 4" [100] PE REFRIG OUT 11"-4 3/4" [3473] 11"-5 3/4" [3499]	3/8" * 10'-5 1/8" [3180] 6" 154] * 7'-2 1/4" [2189]	17'-7 3/8" [5369] 1'-6 1/2" -		13'-11 3/4"		
			FACE B				FACE A		
SHIPPING WEIGHT	61140 lbs+ [27	7735] kg+	OPERATING 78000 lbs+ [35385] k	g+ HEAVIEST SE WEIGH	CTION 27510 lbs+ [1248	0] kg+	NO. OF SHIPPING SECTIONS	4 DI	RAWN BY: SLR